

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: QC/22

Order data

Order number	264834 QC/22
GTIN	4251414902503
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SDQCR

suitable indexable insert: DC.. 0702..

Approach angle: 107.5 °

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre offset L_3 : 13 mm

Technical description

ISO code cutting head	SDQCR
suitable indexable insert	DC.. 0702..

Insert screw	269023 1
Centre offset L ₃	13 mm
System	QC
Series	Master Mute
Approach angle	107.5 °
Minimum pre-drill Ø D _{min}	24 mm
Overall length L	20 mm
Cutting point / joint	20 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamping screw	269431
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 1	269023 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500