

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: QC/20

Order data

Order number	264834 QC/20
GTIN	4251414902411
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SCLCR

suitable indexable insert: CC.. 09T3..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre offset L_3 : 13 mm

Technical description

Approach angle	95 °
Cutting point / joint	20 mm

System	QC
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Overall length L	20 mm
Centre offset L_3	13 mm
Insert screw	269023 2
ISO code cutting head	SCLCR
Series	Master Mute
suitable indexable insert	CC.. 09T3..
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamping screw	269406
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 3	269022 3
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 2	269023 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500