

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: QC/25**

**Order data**

Order number	264834 QC/25
GTIN	4251414902558
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264890; 264894 and 264898.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SDUCR

suitable indexable insert: DC.. 11T3..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 26 mm

Centre offset  $L_3$ : 15 mm

**Technical description**

Cutting point / joint	20 mm
Series	Master Mute

suitable indexable insert	DC.. 11T3..
Approach angle	93 °
Overall length L	20 mm
Minimum pre-drill $\varnothing D_{\min}$	26 mm
ISO code cutting head	SDUCR
Insert screw	269023 2
Centre offset $L_3$	15 mm
System	QC
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 2	269023 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Clamping screw	269432
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500