

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: QC/28

Order data

Order number	264834 QC/28
GTIN	4251414902725
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: STUCR

suitable indexable insert: TC.. 1102..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre offset L_3 : 13 mm

Technical description

Centre offset L_3	13 mm
Insert screw	269023 2

Cutting point / joint	20 mm
Approach angle	93 °
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Overall length L	20 mm
ISO code cutting head	STUCR
suitable indexable insert	TC.. 1102..
Series	Master Mute
System	QC
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamping screw	269407
Insert screw Type 2	269023 2
Insert screw Type 4	269022 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500