

3M**VHB™ adhesive tape, black, Width×length (mm× m): 19X33**

Order data

Order number	083782 19X33
GTIN	4046719048878
Item class	08M

Description

Version:

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5962F** means reliability right across the board. It offers optimum adaptability to the surfaces to be bonded. This feature permits even thin and structured surfaces to be joined without any sort of stress.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request.

Technical description

Storage temperature	20 °C
Application	Sealing
Application	Attaching

Application	Masking
Application	Assembly
temperature-resistant up to	120 - 150 °C
Stretch capability	300 %
Manufacturer's designation	5962F
Storage humidity	50 %
Adhesive strength on steel	5.5 N/mm
Length	33 m
"Best before" date	12 mo
Adhesive	Acrylate
Type of adhesive tape	double-sided
Thickness	1.6 mm
Special features	clings well
Special features	damping
Special features	moisture-resistant
Colour	grey
Width	19 mm
Material of covering	Paper
Product name attribute	black
Type of product	Adhesive tape