

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/45

Order data

| | |
|--------------|---------------|
| Order number | 264838 DM/45 |
| GTIN | 4251414903005 |
| Item class | 29D |

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DWLNR

suitable indexable insert: WN.. 0804..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre offset L_3 : 27 mm

Technical description

| | |
|----------------|-------------|
| Approach angle | 95 ° |
| Series | Master Mute |

| | |
|--|--------------|
| System | DM |
| Overall length L | 35 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 48 mm |
| Cutting point / joint | 40 mm |
| Clamp, screw, O-ring | 259036 3 |
| Shim screw | 259027 4 |
| Shim | 259033 6 |
| suitable indexable insert | WN.. 0804.. |
| Centre offset L_3 | 27 mm |
| ISO code cutting head | DWLN R |
| Application type | right-hand |
| Through-coolant | yes |
| Type of product | Cutting head |

Accessories

| | |
|--|-------------|
| Shim screw Type 4 | 259027 4 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659906 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Insert screw Type 3 | 269022 3 |
| Clamping screw | 269406 |
| Clamp unit Type 5 | 259036 5 |
| Shim Type 6 | 259033 6 |