

**Garant**
**GARANT Master Mute cutting head, left-hand, System / insert size: DM/45**

**Order data**

Order number	264839 DM/45
GTIN	4251414903012
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DWLNL

suitable indexable insert: WN.. 0804..

Approach angle: 95 °

Minimum pre-drill  $\varnothing D_{\min}$ : 48 mm

Centre offset  $L_3$ : 27 mm

**Technical description**

Series	Master Mute
Cutting point / joint	40 mm

suitable indexable insert	WN.. 0804..
Centre offset L <sub>3</sub>	27 mm
Overall length L	35 mm
Shim screw	259027 4
Minimum pre-drill Ø D <sub>min</sub>	48 mm
Clamp, screw, O-ring	259036 17
System	DM
Approach angle	95 °
ISO code cutting head	DWLNL
Shim	259033 6
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

Clamp unit Type 1	259036 1
Shim	259228
Shim screw Type 4	259027 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Shim Type 6	259033 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw	259614
Clamp unit	259502