

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/49

Order data

Order number	264838 DM/49
GTIN	
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Technical description

Cutting point / joint	40 mm
ISO code cutting head	STUCR
Insert screw	269023 3
System	DM
Centre offset L ₃	27 mm
Shim	259033 4
Series	Master Mute

Approach angle	93 °
Shim screw	269015 2
Overall length L	32 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
suitable indexable insert	TC.. 16T3..
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 3	269023 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15