

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: ST/2

Order data

Order number	264826 ST/2
GTIN	2050002058125
Item class	29D

Description
Suitable for :

Boring bar shanks No. 320102; 320103; 320407 and 320408.

Through-coolant: yes

Cutting point / joint: 32 mm

ISO code indexable cutting head: PCLNR

suitable indexable insert: CN.. 1204..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 40 mm

Centre offset L_3 : 22 mm

Technical description

suitable indexable insert	CN.. 1204..
Insert assignment	left-hand and neutral
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Centre offset L_3	22 mm
Lever screw	320611 P01

Lever	320612 P01
ISO code cutting head	PCLNR
Shim	320610 P01
Overall length L	35 mm
Insert size	12 mm
Spring pin	320618 P01
Cutting point / joint	32 mm
Approach angle	95 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Toggle lever No. 4 Type P01	320612 P01
Clamping screw No. 3 Type P01	320611 P01
Tube pin No. 7 Type P01	320618 P01
Intermediate spacer No. 1 Type P01	320610 P01