

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: ST/8

Order data

Order number	264826 ST/8
GTIN	2050002058187
Item class	29D

Description
Suitable for :

Boring bar shanks No. 320102; 320103; 320407 and 320408.

Through-coolant: yes

Cutting point / joint: 40 mm

ISO code cutting head: SCLCR

suitable indexable insert: CC.. 1204..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 27 mm

Technical description

Overall length L	40 mm
Insert size	12 mm
Insert assignment	left-hand and neutral
ISO code cutting head	SCLCR
suitable indexable insert	CC.. 1204..

Minimum pre-drill $\varnothing D_{\min}$	50 mm
Cutting point / joint	40 mm
Insert screw	320620 S01
Centre offset L_3	27 mm
Approach angle	95 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Torx-screw No. 2 Type 2	320620 2
-------------------------	----------