

Garant GRIDLINE

Workbench with undercarriage, height 950 mm with bamboo worktop, 20×20G, Worktop length: 1500mm**Order data**

Order number	923641 1500
GTIN	4062406264918
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section, **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport. Undercarriage is fitted with 2 castors and 2 fixed wheels Ø100 mm with solid rubber tyres. The bench is evenly raised or lowered using the 2-component Haptoprene® lifting handle. This combines high stability at the point of use with the ease of transport. Undercarriage load capacity up to **400 kg** (workbench incl. contents). Feet with plastic pads, do not damage the floor. Drawer casing 24G can be locked centrally with cylinder lock.

Fitted with:

Door height (left) mm: 625

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 100, 125, 150, 250

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **wheels and push handle always RAL 7016 anthracite** (not configurable), **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable width in G	20
--------------------------	----

Individual drawer release system	One-hand
Drawer usable area in G	20×20
Drawer usable depth	500 mm
Drawer body usable height	625 mm
maximum load capacity, mobile unit	400 kg
Drawer usable width	500 mm
Support cabinet depth	700 mm
Weight	173 kg
Support cabinet width	1300 mm
Height	950 mm
Worktop length	1500 mm
Worktop thickness	50 mm
Worktop depth	750 mm
Drawer usable depth in G	20
Nominal voltage	250 V
Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	mobile workbench

