

Garant GRIDLINE

**Casing 24G with door hinged on the left / drawers, 20×20G, Height / number of drawers: 800/2****Order data**

|              |               |
|--------------|---------------|
| Order number | 927612 800/2  |
| GTIN         | 4062406265007 |
| Item class   | 9GG           |

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

**Fitted with:**

Drawer front height, mm: 75#75

Door height, mm: 525

Number of height-adjustable shelves: 1

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

**Technical description**

|       |        |
|-------|--------|
| Width | 600 mm |
|-------|--------|

|  |  |
|--|--|
| Door height                                      | 525 mm   |
| Drawer usable depth in G                         | 20   |
| Usable height for drawers                        | 150 mm   |
| Drawer usable width                              | 500 mm   |
| Drawer usable depth                              | 500 mm   |
| Drawer usable area in G                          | 20×20  |
| Drawer front height                              | 75 mm  |
| Drawer front height                              | 75 mm  |
| Weight   | 50 kg  |
| Number of doors                                  | 1  |
| Door usable height                               | 525 mm   |
| Number of drawers                                | 2  |
| Door stop  | left-hand  |
| Drawer usable width in G                         | 20   |
| Usable width                                     | 550 mm   |
| Height   | 800 mm   |
| Depth  | 650 mm   |
| Drawer/pull-out shelf load capacity              | 75 kg  |
| Drawer runner extension (partial/full extension) | 100 %  |
| Door opening angle                               | 180 degrees  |
| Cylinder lock                                    | modular lock barrel  |
| Colour selection                                 | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                           | 20×20G   |
| Type of product                                  | Workbench casing   |

## Accessories

|                                     |             |
|-------------------------------------|-------------|
| Slide handle for GridLine Type KO12 | 914226 KO12 |
|-------------------------------------|-------------|

|  |                |
|--|----------------|
| Drawer Drawer front height 75 mm   | 927800 75      |
| Casing 24G with door hinged on the left, for individual configuration with drawers Height / door height 800/525 mm | 927727 800/525 |
| Lock plate for GridLine Type KO21  | 914227 KO21    |
| Handle end caps 20 pieces Type 10  | 951025 10      |