

Garant GRIDLINE

Casing 16G with door hinged on the left, for individual configuration with drawers, 12×20G, Height / door height: 900/525mm**Order data**

Order number	927422 900/525
GTIN	4062406264994
Item class	9GG

Description**Version:**

16G cabinet casing with door, for individual configuration with drawers, in sturdy steel construction. Can be locked centrally with a cylinder lock.
Door hinged on the left.

Fitted with:

Number of height-adjustable shelves: 1

Colour:

Body RAL 7035 light grey, door RAL 7016 anthracite **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600/425 and 700/525 suitable only for Ready-to-go workbenches.

Technical description

Weight	29 kg
Usable width	350 mm

Door usable height	525 mm
Depth in G	20
Number of doors	1
Width	400 mm
Width in G	12
Door height	525 mm
Depth	650 mm
Height	900 mm
Number of height-adjustable shelves	1
Usable height for drawers	250 mm
Version	for individual configuration
Material thickness	1 mm
Door opening angle	180 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Fixed shelf, galvanised Type 1	927515 1
Pull-out shelf Type 1	927510 1
Shelf carriers for shelves of workbenches Type 12	927094 12