

Garant GRIDLINE

Casing 24G with door hinged on the left / drawers, 20×20G, Height / number of drawers: 900/3**Order data**

Order number	927612 900/3
GTIN	4062406265021
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

Fitted with:

Drawer front height, mm: 75, 75, 100

Door height, mm: 525

Number of height-adjustable shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Door usable height	525 mm
--------------------	--------

Height	900 mm
Drawer usable area in G	20×20
Door stop	left-hand
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	75 mm
Weight	61 kg
Door height	525 mm
Width	600 mm
Number of doors	1
Drawer usable width in G	20
Number of drawers	3
Drawer usable width	500 mm
Usable width	550 mm
Depth	650 mm
Drawer usable depth	500 mm
Usable height for drawers	250 mm
Drawer usable depth in G	20
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 100 mm	927800 100
Casing 24G with door hinged on the left, for individual configuration with drawers Height / door height 900/525 mm	927727 900/525
Lock plate for GridLine Type KO21	914227 KO21
Handle end caps 20 pieces Type 10	951025 10