

Garant GRIDLINE

Casing 24G with door hinged on the left, Height / number of drawers: 600**Order data**

Order number	927617 600
GTIN	4062406265038
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

Fitted with:

Door height, mm: 525

Number of height-adjustable shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Door usable height	525 mm
Usable width	550 mm

Depth	650 mm
Number of doors	1
Number of drawers	0
Width	600 mm
Door height	525 mm
Usable height	525 mm
Height	600 mm
Weight	26 kg
Door stop	left-hand
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
-------------------------------------	-------------