

Garant GRIDLINE

Casing 24G with door hinged on the left, Height / number of drawers: 900**Order data**

Order number	927617 900
GTIN	4062406265069
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

Fitted with:

Door height, mm: 800

Number of height-adjustable shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Door stop	left-hand
Usable height	800 mm

Width	600 mm
Door height	800 mm
Number of doors	1
Depth	650 mm
Usable width	550 mm
Weight	34 kg
Door usable height	800 mm
Number of drawers	0
Height	900 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
-------------------------------------	-------------