

SWISS TOOLS

Cutting head, left-hand, System / insert size: ST/11



Order data

Order number	264827 ST/11
GTIN	2050002059351
Item class	29D

Description

Suitable for:

Boring bar shanks No. 320102, 320104, 320407, 320409 and 320410.

Spare part:

Insert screw on request.

Technical description

Cutting point / joint	40 mm
ISO code cutting head	SDQCL
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Centre offset L_3	27 mm
Insert assignment	right-hand and neutral
Overall length L	40 mm

Approach angle	107.5 degrees
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head