

Garant GRIDLINE**Casing 24G with door hinged on the left, for individual configuration with drawers, 20×20G, Height / door height: 600/425mm****Order data**

Order number	927727 600/425
GTIN	4062406266134
Item class	9GG

**Description****Version:**

24G casing with cupboard, for individual configuration with drawers in sturdy steel construction. Can be locked centrally with cylinder lock.

Door hinged on the left.

**Colour:**

Body RAL 7035 light grey, door RAL 7016 anthracite **powder-coated**.

**Note:**

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600/425 and 700/525 suitable only for Ready-to-go workbenches.

**Technical description**

Depth	650 mm
Weight	26 kg
Width	600 mm
Door usable height	425 mm

Usable height for drawers	75 mm
Height	600 mm
Usable width	550 mm
Version	for individual configuration
Material thickness	1 mm
Door opening angle	180 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench casing

---

## Accessories

Slide handle for GridLine Type KO12	914226 KO12
-------------------------------------	-------------