

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/42

Order data

Order number	264838 DM/42
GTIN	4251414902671
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DDUNR

suitable indexable insert: DN.. 1506..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 48 mm

Centre offset L_3 : 27 mm

Technical description

Shim	259033 3
Approach angle	93 °

Minimum pre-drill $\varnothing D_{\min}$	48 mm
Cutting point / joint	40 mm
Centre offset L_3	27 mm
Clamp, screw, O-ring	259036 4
Shim screw	259027 2
Overall length L	35 mm
System	DM
ISO code cutting head	DDUNR
suitable indexable insert	DN.. 1506..
Series	Master Mute
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Shim Type 3	259033 3
Clamp unit Type 4	259036 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw	259612
Shim screw Type 2	259027 2
Shim	259225
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Clamp unit	259506