


**Kroeplin**  
Längenmesstechnik

## External quick caliper with dial gauge, Measuring range: 0-50mm



### Order data

Order number	438555 0-50
GTIN	2050002043459
Item class	46Q

### Description

#### Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Application:

For quick measuring of external grooves, wall thicknesses, plates, pipe wall thicknesses, foils etc.

### Technical description

maximum contact point length L (measurement depth)	167 mm
Measuring range	0 - 50 mm
Error limit	0.05 mm
Scale divisions	0.05 mm
Carbide spherical point $\varnothing$	3 mm
Dial indicator $\varnothing$	66 mm
IP Index of Protection	IP 65
Standard	Manufacturer's standard

Measurement technology	analogue
Calibration	C7
Type of product	External quick callipers

**Services**

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S