

Kroepelin
Längenmesstechnik

Digital internal quick caliper, Measuring range: 5-15mm



Order data

Order number	438965 5-15
GTIN	2050002040960
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 2 batteries No. 081561 size LR3, operating instructions.

Optional extras:

Data cable adapter No. 498954 size A2; data cable No. 497440; radio adapter No. 498954 size A5.

Technical description

Number of batteries contained	2
Error limit	0.015 mm
Carbide spherical point \varnothing	0.6 mm
minimum groove width	0.8 mm
maximum contact point length L (measurement depth)	35 mm
Measuring range	5 - 15 mm

Article no of the battery / rechargeable battery fitted	081561 LR3
Gauging force	0.8 - 1.2 N
maximum groove depth	2.3 mm
Repetition accuracy	0.005 mm
IP Index of Protection	IP 67
Power supply	Battery-powered
Graduations can be switched over	0.02 mm
Graduations can be switched over	0.002 mm
Graduations can be switched over	0.01 mm
Graduations can be switched over	0.005 mm
Graduations can be switched over	0.05 mm
Graduations can be switched over	0.001 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Bluetooth interface
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	Internal quick caliper

Services

DAkkS calibration External / internal quick caliper Type S	023460 S
Calibration External / internal quick caliper Type S	023450 S

Accessories

Connecting cable Type USB2	497440 USB2
Receiver / USB keyboard interface Type	498965

Multi-receiver / USB keyboard interface Type	498975
Connecting cable Type D1	497440 D1
Interface adapter Type A2	498954 A2
Alkaline-manganese batteries International size LR3	081561 LR3
Connecting cable Type D2	497440 D2