

Digital internal quick caliper with 3-point contact, Measuring range: 7-14mm

Order data

Order number	438985 7-14
GTIN	2050002041011
Item class	46Q

Description
Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

3-point contact for quick and reliable determination of the measured value.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 2 batteries No. 081561 size LR3, operating instructions.

Optional extras:

Data cable adapter No. 498954 size A2; data cable No. 497440; radio adapter No. 498954 size A5.

Technical description

maximum groove depth	2.2 mm
minimum groove width	0.8 mm
Repetition accuracy	0.004 mm
Gauging force	1 - 1.4 N
Error limit	0.01 mm

#Article no of the battery / rechargeable battery fitted	081561 LR3
Measuring range	7 - 14 mm
maximum contact point length L (measurement depth)	34 mm
#Number of batteries contained	2
Measurement contact profile	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Graduations can be switched over	0.002 mm
Graduations can be switched over	0.001 mm
Graduations can be switched over	0.005 mm
Graduations can be switched over	0.05 mm
Graduations can be switched over	0.02 mm
Graduations can be switched over	0.01 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Bluetooth® interface
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Test certificate	Manufacturer's test certificate
Type of product	Internal quick caliper

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/438985-7-14>