

**Electrical insulating tape, Width×length (mm× m): 19X6****Order data**

Order number	083656 19X6
GTIN	50054007061309
Item class	08M

Description**Version:**

3M Scotch® Super 88 and **Scotch® Super 33+** are particularly resilient and UV-resistant premium adhesive tapes with very good electrical characteristics and resistance to moisture, alkalis, many acids and solvents.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Thickness: 0.18 mm

Technical description

Thickness	0.18 mm
Width	19 mm
Backing material	PVC film
Storage humidity	75 %
Manufacturer's designation	Scotch® Super 33+

Data sheet

Storage temperature	10 - 27 °C
temperature-resistant up to	-18 - 90 °C
"Best before" date	60 mo
Special features	UV-resistant
Special features	moisture-resistant
Type of adhesive tape	single-sided
Length	6 m
Liner present	no
Colour	black
Type of product	Adhesive tape