

**Electrical insulating tape, Width×length (mm× m): 19X33****Order data**

|              |                |
|--------------|----------------|
| Order number | 083656 19X33   |
| GTIN         | 50054007000537 |
| Item class   | 08M            |

**Description****Version:**

**3M Scotch® Super 88** and **Scotch® Super 33+** are particularly resilient and UV-resistant premium adhesive tapes with very good electrical characteristics and resistance to moisture, alkalis, many acids and solvents.

**Note:**

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Thickness: 0.18 mm

**Technical description**

|                       |              |
|-----------------------|--------------|
| Backing material      | PVC film     |
| Type of adhesive tape | single-sided |
| Storage humidity      | 75 %         |
| Length                | 33 m         |
| "Best before" date    | 60 mo        |

|                             |                    |
|-----------------------------|--------------------|
| Manufacturer's designation  | Scotch® Super 33+  |
| Width                       | 19 mm              |
| temperature-resistant up to | -18 - 90 °C        |
| Special features            | UV-resistant       |
| Special features            | moisture-resistant |
| Storage temperature         | 10 - 27 °C         |
| Thickness                   | 0.18 mm            |
| Colour                      | black              |
| Liner present               | no                 |
| Type of product             | Adhesive tape      |