

Garant**Abrasive cap (CER), 220 grit, Abrasive cap Ø, length, form: 1626G****Order data**

| | |
|--------------|---------------|
| Order number | 553040 1626G |
| GTIN | 4062406271749 |
| Item class | 51E |

Description**Version:**

Optimised grit bonding yields very aggressive abrasion and a high material removal rate.

Ceramic grit (CER) ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

Application:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. The **abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Note:

Compatible only for use with ground abrasive cap holder No. 553100.

Technical description

| | |
|---------------------|-------------------------|
| recommended speed | 12000 min ⁻¹ |
| Abrasive cap length | 26 mm |
| Abrasive cap Ø | 16 mm |
| Shape | G |

| | |
|------------------------|--------------|
| Grit | 220 |
| Product name attribute | 220 grit |
| Type of product | Abrasive cap |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable only under restricted conditions | | |
| dry | suitable | | |