



Core LED torch with rechargeable battery, Type: P5R-CORE



Order data

Order number	081468 P5R-CORE
GTIN	4058205020428
Item class	04B

Description

Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Core series Ledlenser, the new generation of the well-known P series.

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable and wrist strap.

Technical description

Power supply	Rechargeable battery-powered
Battery voltage	3.7 V
ATEX zone	no
Illumination	350 lm
Manufacturer's designation	P5R-CORE
Number of rechargeable batteries contained	1
Illumination time stage 2	3.5 h
Bulb	LED module
IP Index of Protection	IP 68

Battery capacity	0.75 Ah
Advanced Focus System (AFS)	yes
Weight	106 g
Illumination time	1 h
Smart Light Technology (SLT)	yes
Overall length	123 mm
Type of rechargeable battery	Lithium-ion
Head Ø	29 mm
Illumination step 2	130 lm
Illumination time stage 3	25 h
Illumination step 3	15 lm
Type of product	Flashlight