

**Garant****Flap wheel Fleece (ZA), fine, Head  $\varnothing$ ×head width: 50X20mm****Order data**

Order number	554908 50X20
GTIN	4062406272364
Item class	51E

**Description****Version:**

Flap strips of fleece around the shank of the tool. Shank  $\varnothing$  6 mm.

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). **Ideal for use on stainless steel.**

**Application:**

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

**Technical description**

Shank $\varnothing$	6 mm
maximum speed	11000 min <sup>-1</sup>
recommended speed	6000 min <sup>-1</sup>
Head $\varnothing$	50 mm
Head width	20 mm
Grinding medium code	ZA
Grit equivalent	280
Grit designation	fine

Product name attribute	fine
Type of product	Flap wheel

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		