



Core LED torch with rechargeable battery, Type: P6R-CORE



Order data

Order number	081468 P6R-CORE
GTIN	4058205020459
Item class	04B

Description

Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Core series Ledlenser, the new generation of the well-known P series.

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable and wrist strap.

Technical description

Battery voltage	3.7 V
Manufacturer's designation	P6R-CORE
Head Ø	35 mm
Battery capacity	2.5 Ah
ATEX zone	no
Illumination	600 lm
IP Index of Protection	IP 68
Overall length	151 mm
Illumination step 2	240 lm

Weight	170 g
Illumination time	2 h
Number of rechargeable batteries contained	1
Smart Light Technology (SLT)	yes
Type of rechargeable battery	Lithium-ion
Illumination time stage 2	6 h
Bulb	LED module
Advanced Focus System (AFS)	yes
Power supply	Rechargeable battery-powered
Illumination step 3	15 lm
Illumination time stage 3	95 h
Type of product	Flashlight