

Garant GRIDLINE

Casing 16G with door hinged on the left / drawers, 12×20G, Height / number of drawers: 900/2**Order data**

Order number	927307 900/2
GTIN	4062406272449
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

Fitted with:

Drawer front height, mm: 75#75

Door height, mm: 625

Number of height-adjustable shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Height	900 mm
--------	--------

Width	400 mm
Depth	650 mm
Drawer usable width	300 mm
Usable width	350 mm
Number of drawers	2
Drawer usable depth	500 mm
Drawer usable width in G	12
Drawer usable depth in G	20
Weight	43.7 kg
Number of doors	1
Usable height for drawers	150 mm
Drawer front height	75 mm
Drawer front height	75 mm
Door stop	left-hand
Drawer usable area in G	12×20
Door usable height	625 mm
Door height	625 mm
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 75 mm	927500 75
Handle end caps 20 pieces Type 10	951025 10
Lock plate for GridLine Type KO21	914227 KO21