

Garant GRIDLINE

**Casing 16G with door hinged on the left, Height / number of drawers: 700****Order data**

|              |               |
|--------------|---------------|
| Order number | 927312 700    |
| GTIN         | 4062406272470 |
| Item class   | 9GG           |

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

**Fitted with:**

Door height, mm: 625

Number of height-adjustable shelves: 1

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

**Technical description**

|                    |        |
|--------------------|--------|
| Door usable height | 625 mm |
| Width              | 400 mm |

|  |   |
|--|---|
| Door height                                      | 625 mm  |
| Usable height                                    | 625 mm  |
| Number of doors                                  | 1   |
| Height   | 700 mm  |
| Usable width                                     | 350 mm  |
| Number of drawers                                | 0   |
| Door stop  | left-hand   |
| Weight   | 23.7 kg   |
| Depth  | 650 mm  |
| Material thickness                               | 1 mm  |
| Drawer/pull-out shelf load capacity              | 75 kg   |
| Drawer runner extension (partial/full extension) | 100 %   |
| Door opening angle                               | 180 degrees   |
| Cylinder lock                                    | modular lock barrel   |
| Colour selection                                 | RAL 9002, 7035, 7005, 7016, 6011,<br>5018, 5012, 5011, 5005, 3003 |
| Type of product                                  | Workbench casing  |

## Accessories

|   |             |
|---|-------------|
| Slide handle for GridLine Type KO12               | 914226 KO12 |
| Shelf carriers for shelves of workbenches Type 12 | 927094 12   |
| Fixed shelf, galvanised Type 1                    | 927515 1    |