

Garant GRIDLINE

**Casing 16G with door hinged on the left, Height / number of drawers: 600****Order data**

Order number	927312 600
GTIN	4062406272463
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the left.

**Fitted with:**

Door height, mm: 525

Number of height-adjustable shelves: 1

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

**Technical description**

Number of doors	1
Door height	525 mm

Number of drawers	0
Usable width	350 mm
Door usable height	525 mm
Usable height	525 mm
Depth	650 mm
Width	400 mm
Weight	21.4 kg
Door stop	left-hand
Height	600 mm
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

## Accessories

Slide handle for GridLine Type KO12	914226 KO12
Shelf carriers for shelves of workbenches Type 12	927094 12
Fixed shelf, galvanised Type 1	927515 1