



LED torch, Type: P4R



Order data

Order number	081467 P4R
GTIN	4058205023740
Item class	04B

Description

Version:

Compact torches in bar format or key fob format.

· **Optionally as a disposable battery or rechargeable battery version.**

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with charging station and USB charging cable.

Technical description

Manufacturer's designation	P4R
Battery voltage	1.2 V
Type of rechargeable battery	Nickel metal hydride
Illumination	120 lm
Weight	60 g
Battery capacity	0.9 Ah
Overall length	146 mm
Illumination time stage 2	18 h

Advanced Focus System (AFS)	yes
Bulb	LED module
Illumination time	4 h
Number of rechargeable batteries contained	2
Head Ø	15 mm
Illumination step 2	10 lm
IP Index of Protection	IP 54
ATEX zone	no
Smart Light Technology (SLT)	no
Power supply	Rechargeable battery-powered
Type of product	Flashlight

Accessories

Set of NiMH rechargeable batteries pre-charged International size LR3	081575 LR3
Set of NiMH rechargeable batteries International size LR3	081570 LR3