



## Flap wheel (A), 150 grit, Head Ø×head width: 15X10mm



### Order data

Order number	555035 15X10
GTIN	4027497608836
Item class	56L

### Description

#### Version:

Flap strips bonded on to the shank of the tool. Inserted strips bonded at the end.

#### Application:

Deburring of holes, cross holes and pipe internal diameters. The abrasive strips adapt to the diameter of the component. Radial use.

### Technical description

Shank Ø	6 mm
maximum speed	18000 min <sup>-1</sup>
Overall length	100 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	150 grit
Type of product	Flap wheel

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		

Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable only under restricted conditions
GG(G)	suitable only under restricted conditions
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
dry	suitable