



Digital dial indicator 0.01 mm reading, Measuring range: 25mm



Order data

Order number	434004 25
GTIN	4062406272500
Item class	42C

Description

Version:

Digital dial indicator in compact design with high-contrast digital display.

- **Reversible direction of measurement.**
- **Very narrow casing.**

Version of the advertising text:

Digital dial indicator in compact design with high-contrast digital display.

Supplied with:

Supplied with an eye on the cover and 1 battery No. 081560 size CR2032.

Optional extras:

Spare and special contact points No. 434900; 434910; 434915.

Technical description

Reversible reading	0.0005 in
Clamping shank - \varnothing h7	8 mm
Gauging force	0.8 – 1.7 N
Measuring range	0 - 25 mm

Body Ø	58 mm
Calibration	C1
Number of batteries contained	1
Reversible reading	0.01 mm
Thickness of housing	26 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Measurement variation E MPE (measurement range)	0.035 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100

Accessories

Steel contact point Type 12	434900 12
Extension for contact points Length L 70 mm	434920 70
Angled bracket for dial indicator45° Clamping length 50 mm	434917 50
Ruby contact point Type 2	434915 2
Steel contact point Type 14	434900 14
Pivoting contact point	434912
Steel contact point Type 2	434900 2
Carbide contact point Type 17	434910 17

Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25
Button cell / special battery Battery type CR2032	081560 CR2032
Steel contact point Type 13	434900 13
Extension for contact points Length L 30 mm	434920 30
Extension for contact points Length L 10 mm	434920 10
Extension for contact points Length L 60 mm	434920 60
Steel contact point Type 15	434900 15
Steel contact point Type 16	434900 16
Extension for contact points Length L 20 mm	434920 20
Carbide contact point Type 10	434910 10
Extension for contact points Length L 100 mm	434920 100
Carbide contact point Type 2	434910 2
Steel contact point Type 11	434900 11
Steel contact point Type 39	434900 39
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Extension for contact points Length L 15 mm	434920 15
Carbide contact point Type 16	434910 16
Carbide contact point Type 11	434910 11
Steel contact point Type 10	434900 10
Steel contact point Type 20	434900 20
Extension for contact points Length L 50 mm	434920 50
Steel contact point Type 28	434900 28
Extension for contact points Length L 40 mm	434920 40
Steel contact point Type 17	434900 17
Carbide contact point Type 14	434910 14
Extension for contact points Length L 90 mm	434920 90
Steel contact point Type 24	434900 24
	434917 25

Angled bracket for dial indicator 45° Clamping length 25 mm

Extension for contact points Length L 80 mm

434920 80