



Work LED torch with rechargeable battery, Type: P18R-WORK



Order data

Order number	081469 P18R-WORK
GTIN	4058205020749
Item class	04B

Description

Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Work series LED lenses, virtually indestructible lamps for use in the rough industrial environment.

- **Rubber covering around the lamp head and on the end cap provide protection against impacts and damage.**
- **Additional front screen protects the lens against scratches.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB charging cable and wrist strap.

Technical description

Illumination time stage 2	4.5 h
Illumination	2600 lm
Battery capacity	3 Ah
IP Index of Protection	IP 54
Bulb	LED module

Number of rechargeable batteries contained	1
ATEX zone	no
Illumination step 2	1000 lm
Illumination time	2.5 h
Head Ø	99 mm
Weight	669 g
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	P18R-WORK
Advanced Focus System (AFS)	yes
Power supply	Rechargeable battery-powered
Overall length	183 mm
Battery voltage	3.7 V
Smart Light Technology (SLT)	yes
Illumination step 3	30 lm
Illumination time stage 3	70 h
Type of product	Flashlight