



Work LED torch with rechargeable battery, Type: P7R-WORK



Order data

Order number	081469 P7R-WORK
GTIN	4058205020695
Item class	04B

Description

Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Work series LED lenses, virtually indestructible lamps for use in the rough industrial environment.

- **Rubber covering around the lamp head and on the end cap provide protection against impacts and damage.**
- **Additional front screen protects the lens against scratches.**

Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable, wrist strap and charging station.

Technical description

Illumination	900 lm
Overall length	170 mm
Illumination step 2	390 lm
Number of rechargeable batteries contained	1
Battery voltage	3.7 V
ATEX zone	no
Illumination time stage 2	3.25 h

Advanced Focus System (AFS)	yes
Type of rechargeable battery	Lithium-ion
Smart Light Technology (SLT)	yes
Illumination time	2 h
Power supply	Rechargeable battery-powered
Bulb	LED module
Manufacturer's designation	P7R-WORK
Battery capacity	4.8 Ah
Weight	219 g
IP Index of Protection	IP 68
Head Ø	45 mm
Illumination time stage 3	60 h
Illumination step 3	15 lm
Type of product	Flashlight