

Garant GRIDLINE

Roller cabinet for drawers, 46×24G, Height mm / number of drawers: 885/0**Order data**

Order number	931427 885/0
GTIN	4062406352745
Item class	9GK

Description**Version:**

To take drawers 46×24G.

Roller cabinet in 50×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

May only be fitted with drawer No. 931454 or No. 931456 (with one-handed individual drawer release system).

Technical description

maximum load capacity	600 kg
ComfortClose	no
Number of drawers	0
Weight	81 kg

Treadless tyres	yes
Depth	700 mm
Height	885 mm
Wheel Ø	125 mm
Number of castors with parking brake	2
Electronic locking system can be retrofitted	yes
Drawer body height	700 mm
Number of fixed wheels without parking brake	2
Usable height	600 mm
Number of doors	0
with anti-roll lip	yes
Drawer body usable height	600 mm
Width	1250 mm
Version	wheeled
Version	for individual configuration
Number of pull-out shelves	0
Usable height for drawers	600 mm
Casing open at the top	no
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	46x24G
Type of product	Assembly trolley

Accessories

Sheet metal cover top with raised edge on 4 sides
Dimension in G 50X28

951972 50X28