

Garant GRIDLINE

**Roller cabinet with drawers 75 kg, 20×20G, Height mm / number of drawers:
685/3****Order data**

Order number	930515 685/3
GTIN	4062406352479
Item class	9GK

Description**Version:****Complete with drawers 20×20G.**

Roller cabinet in 24×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Fitted with:

Drawer front height, mm: 100, 100, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Weight	68 kg
Drawer body usable height	400 mm
maximum load capacity	600 kg
Drawer usable width in G	20
Drawer/pull-out shelf load capacity	75 kg
Number of drawers	3
Width	600 mm
Drawer usable area in G	20×20
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes
Depth	600 mm
Drawer usable depth in G	20
Treadless tyres	yes
Individual drawer release system	One-hand
Usable height	400 mm
Number of doors	0
Drawer body height	500 mm
Drawer usable width	500 mm
Height	685 mm
Drawer runner extension (partial/full extension)	100 %
with anti-roll lip	yes
Wheel Ø	125 mm
ComfortClose	no
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	400 mm

Casing open at the top	no
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Assembly trolley

Accessories

Push handle Type 1	958490 1
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system,75 kg Drawer front height 100 mm	930534 100
Drawer with one-handed individual drawer release system,75 kg Drawer front height 200 mm	930534 200
Roller cabinet for drawers Height mm / number of drawers 685/0	930517 685/0
Sheet metal cover top with raised edge on 4 sides Dimension in G 24X24	951972 24X24