

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 20×20G, Height mm / number of drawers: 685/4



Order data

Order number	930515 685/4
GTIN	4062406348748
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Complete with drawers 20×20G.

Roller cabinet in 24×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Fitted with:

Drawer front height, mm: 50, 100, 100, 150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 685 mm

Width: 600 mm

Depth: 600 mm

Usable height: 400 mm

Drawer body height: 500 mm

Drawer body usable height: 400 mm

Technical description

Wheel Ø	125 mm
Drawer body height	500 mm
maximum load capacity	600 kg
Number of doors	0
Electronic locking system can be retrofitted	yes
Drawer/pull-out shelf load capacity	75 kg
Depth	600 mm
Height	685 mm
Drawer usable width	500 mm
Drawer body usable height	400 mm
Drawer usable depth in G	20
Drawer usable area in G	20×20
Individual drawer release system	One-hand
Usable height	400 mm
Weight	76 kg
Number of castors with parking brake	2
Width	600 mm
Drawer runner extension (partial/full extension)	100 %
Number of drawers	4
Treadless tyres	yes
Drawer usable depth	500 mm
ComfortClose	no

Drawer usable width in G	20
Number of fixed wheels without parking brake	2
with anti-roll lip	yes
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Casing open at the top	no
Usable height for drawers	400 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G

Accessories

One-hand individual drawer release system Drawer usable width in G 20	951020 20
Lock plate for GridLine Type HU21	914227 HU21
Push handle Type 1	958490 1
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	930534 100
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm	930534 150
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 50 mm	930534 50
Roller cabinet for drawers Height mm / number of drawers 685/0	930517 685/0
	951972 24X24

Sheet metal cover top with anti-roll lip on 4 sides
Dimension in G 24X24
