

Garant GRIDLINE

Roller cabinet for drawers, 20×20G, Height mm / number of drawers: 885/0



Order data

Order number	930517 885/0
GTIN	4062406352509
Item class	9GK

Description

Version:

To take drawers 20×20G.

Roller cabinet in 24×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

May only be fitted with drawer No. 930534 (with one-handed individual drawer release system).

Technical description

Number of castors with parking brake	2
Drawer body height	700 mm
maximum load capacity	600 kg
Number of fixed wheels without parking brake	2

Electronic locking system can be retrofitted	yes
with anti-roll lip	yes
Width	600 mm
Number of doors	0
Drawer body usable height	600 mm
Depth	600 mm
Number of drawers	0
Height	885 mm
Treadless tyres	yes
Usable height	600 mm
Wheel Ø	125 mm
ComfortClose	no
Weight	48 kg
Version	wheeled
Version	for individual configuration
Casing open at the top	no
Usable height for drawers	600 mm
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Assembly trolley

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Push handle Type 1	958490 1
Sheet metal cover top with raised edge on 4 sides Dimension in G 24X24	951972 24X24