

Garant GRIDLINE

Roller cabinet for drawers, 36×24G, Height mm / number of drawers: 885/0**Order data**

| | |
|--------------|---------------|
| Order number | 931327 885/0 |
| GTIN | 4062406352714 |
| Item class | 9GK |

Description**Version:**

To take drawers 36×24G.

Roller cabinet in 40×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

May only be fitted with drawer No. 931354 or No. 931356 (with one-handed individual drawer release system).

Technical description

| | |
|-------------------|--------|
| Height | 885 mm |
| Depth | 700 mm |
| ComfortClose | no |
| Number of drawers | 0 |

| | |
|--|--|
| Drawer body height | 700 mm |
| with anti-roll lip | yes |
| Number of fixed wheels without parking brake | 2 |
| Wheel Ø | 125 mm |
| Weight | 76 kg |
| Number of doors | 0 |
| Number of castors with parking brake | 2 |
| Drawer body usable height | 600 mm |
| Electronic locking system can be retrofitted | yes |
| Width | 1000 mm |
| maximum load capacity | 600 kg |
| Usable height | 600 mm |
| Treadless tyres | yes |
| Version | wheeled |
| Version | for individual configuration |
| Number of pull-out shelves | 0 |
| Casing open at the top | no |
| Usable height for drawers | 600 mm |
| Material thickness | 1.2 mm |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 36x24G |
| Type of product | Assembly trolley |

Accessories

Sheet metal cover top with raised edge on 4 sides
Dimension in G 40X28

951972 40X28