

Garant GRIDLINE

**Roller cabinet with drawers 75 kg, 26×20G, Height mm / number of drawers:
885/5****Order data**

| | |
|--------------|---------------|
| Order number | 930615 885/5 |
| GTIN | 4062406348755 |
| Item class | 9GK |

Description**Version:****Complete with drawers 26×20G.**

Roller cabinet in 30×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Fitted with:

Drawer front height, mm: 75, 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|--|--------------|
| Individual drawer release system | One-hand |
| Number of drawers | 5 |
| Usable height | 600 mm |
| Drawer body height | 700 mm |
| Number of fixed wheels without parking brake | 2 |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer body usable height | 600 mm |
| Treadless tyres | yes |
| Drawer usable area in G | 26×20 |
| Drawer usable depth in G | 20 |
| Drawer/pull-out shelf load capacity | 75 kg |
| Depth | 600 mm |
| Drawer usable width | 650 mm |
| Number of doors | 0 |
| Weight | 106 kg |
| Drawer usable depth | 500 mm |
| with anti-roll lip | yes |
| Drawer usable width in G | 26 |
| Width | 750 mm |
| Height | 885 mm |
| ComfortClose | no |
| Number of castors with parking brake | 2 |
| maximum load capacity | 600 kg |
| Electronic locking system can be retrofitted | yes |
| Version | wheeled |
| Version | with drawers |
| Usable height for drawers | 600 mm |
| Casing open at the top | no |
| Number of pull-out shelves | 0 |

| | |
|----------------------------|--|
| Material thickness | 1.2 mm |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 26x20G |
| Type of product | Assembly trolley |

Accessories

| | |
|--|--------------|
| Drawer with one-handed individual drawer release system,75 kg Drawer front height 150 mm | 930634 150 |
| Lock plate for GridLine Type HU21 | 914227 HU21 |
| Drawer with one-handed individual drawer release system,75 kg Drawer front height 75 mm | 930634 75 |
| Drawer with one-handed individual drawer release system,75 kg Drawer front height 100 mm | 930634 100 |
| Drawer with one-handed individual drawer release system,75 kg Drawer front height 200 mm | 930634 200 |
| Roller cabinet for drawers Height mm / number of drawers 885/0 | 930617 885/0 |
| Sheet metal cover top with raised edge on 4 sides Dimension in G 30X24 | 951972 30X24 |
| Handle end caps20 pieces Type 10 | 951025 10 |