

Garant GRIDLINE

### Roller cabinet with drawers 75 kg, 26×20G, Height mm / number of drawers: 885/4



#### Order data

Order number	930615 885/4
GTIN	4062406352516
Item class	9GK

#### Description

##### Version:

##### Complete with drawers 26×20G.

Roller cabinet in 30×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

**100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

##### Fitted with:

Drawer front height, mm: 75, 100, 125, 300

##### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Technical description

## Data sheet

Number of doors	0
Electronic locking system can be retrofitted	yes
Drawer usable width	650 mm
Drawer body usable height	600 mm
Drawer usable depth in G	20
Depth	600 mm
Drawer/pull-out shelf load capacity	75 kg
maximum load capacity	600 kg
Drawer usable width in G	26
ComfortClose	no
Drawer body height	700 mm
with anti-roll lip	yes
Treadless tyres	yes
Drawer runner extension (partial/full extension)	100 %
Individual drawer release system	One-hand
Number of drawers	4
Usable height	600 mm
Drawer usable depth	500 mm
Drawer usable area in G	26×20
Height	885 mm
Number of fixed wheels without parking brake	2
Width	750 mm
Number of castors with parking brake	2
Weight	95 kg
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	600 mm
Casing open at the top	no

## Data sheet

Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Product name attribute	26×20G
Type of product	Assembly trolley

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/930615-885/4>