

Garant GRIDLINE

## Roller cabinet with drawers 75 kg, 26×24G, Height mm / number of drawers: 985/4



### Order data

Order number	931145 985/4
GTIN	4062406352646
Item class	9GK

### Description

#### Version:

#### Complete with drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

**100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

maximum load capacity	600 kg
with anti-roll lip	yes

Drawer usable depth in G	24
Drawer body height	800 mm
Individual drawer release system	One-hand
Weight	115 kg
ComfortClose	no
Number of castors with parking brake	2
Drawer body usable height	700 mm
Drawer usable width in G	26
Drawer/pull-out shelf load capacity	75 kg
Depth	700 mm
Width	750 mm
Number of doors	0
Treadless tyres	yes
Drawer usable depth	600 mm
Drawer runner extension (partial/full extension)	100 %
Height	985 mm
Number of fixed wheels without parking brake	2
Usable height	700 mm
Number of drawers	4
Drawer usable area in G	26×24
Drawer usable width	650 mm
Wheel Ø	125 mm
Electronic locking system can be retrofitted	yes
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	700 mm
Casing open at the top	no
Material thickness	1.2 mm

Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Assembly trolley

## Accessories

Roller cabinet for drawers Height mm / number of drawers 985/0	931147 985/0
Drawer with one-handed individual drawer release system,75 kg Drawer front height 125 mm	931166 125
Drawer with one-handed individual drawer release system,75 kg Drawer front height 200 mm	931166 200
Drawer with one-handed individual drawer release system,75 kg Drawer front height 300 mm	931166 300
Drawer with one-handed individual drawer release system,75 kg Drawer front height 75 mm	931166 75
Sheet metal cover top with raised edge on 4 sides Dimension in G 30X28	951972 30X28