

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 26×24G, Height mm / number of drawers: 685/3



Order data

Order number	931145 685/3
GTIN	4062406352615
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Complete with drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 26×24

Height: 685 mm

Width: 750 mm
 Depth: 700 mm
 Usable height: 400 mm
 Drawer body height: 500 mm
 Drawer body usable height: 400 mm

Technical description

Number of fixed wheels without parking brake	2
Weight	89 kg
Number of drawers	3
ComfortClose	no
Drawer usable depth	600 mm
Depth	700 mm
Treadless tyres	yes
Electronic locking system can be retrofitted	yes
maximum load capacity	600 kg
Height	685 mm
Drawer usable area in G	26×24
Drawer runner extension (partial/full extension)	100 %
Usable height	400 mm
Drawer body usable height	400 mm
Width	750 mm
Drawer usable depth in G	24
Number of doors	0
Wheel Ø	125 mm
Drawer usable width	650 mm
Individual drawer release system	One-hand
Drawer usable width in G	26
Drawer body height	500 mm
Number of castors with parking brake	2
Drawer/pull-out shelf load capacity	75 kg

with anti-roll lip	yes
Version	wheeled
Version	with drawers
Usable height for drawers	400 mm
Casing open at the top	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G

Accessories

Drawer with one-handed individual drawer release system, 75 kg Drawer front height 200 mm	931166 200
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	931166 100
Roller cabinet for drawers Height mm / number of drawers 685/0	931147 685/0
Sheet metal cover top with anti-roll lip on 4 sides Dimension in G 30X28	951972 30X28