

Garant GRIDLINE

**Roller cabinet with drawers 75 kg, 36×20G, Height mm / number of drawers:  
885/5****Order data**

Order number	930725 885/5
GTIN	4062406348762
Item class	9GK

**Description****Version:****Complete with drawers 36×20G.**

Roller cabinet in 40×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

**100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

**Fitted with:**

Drawer front height, mm: 75, 75, 100, 150, 200

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Number of castors with parking brake	2
--------------------------------------	---

Weight	131 kg
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Number of drawers	5
Drawer usable width in G	36
ComfortClose	no
Drawer body height	700 mm
Treadless tyres	yes
Drawer usable width	900 mm
maximum load capacity	600 kg
Height	885 mm
Depth	600 mm
Width	1000 mm
with anti-roll lip	yes
Electronic locking system can be retrofitted	yes
Usable height	600 mm
Drawer usable depth in G	20
Drawer usable depth	500 mm
Wheel Ø	125 mm
Number of doors	0
Individual drawer release system	One-hand
Drawer usable area in G	36×20
Drawer body usable height	600 mm
Number of fixed wheels without parking brake	2
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	600 mm
Casing open at the top	no

Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x20G
Type of product	Assembly trolley

## Accessories

Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm	930744 150
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	930744 100
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	930744 75
Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 200 mm	930744 200
Roller cabinet for drawers Height mm / number of drawers 885/0	930727 885/0
Sheet metal cover top with raised edge on 4 sides Dimension in G 40X24	951972 40X24