

Garant GRIDLINE

Roller cabinet for drawers, 26×24G, Height mm / number of drawers: 685/0**Order data**

Order number	931147 685/0
GTIN	4062406352677
Item class	9GK

Description**Version:**

To take drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

May only be fitted with drawer No. 931166 or No. 931168 (with one-handed individual drawer release system).

Technical description

Wheel Ø	125 mm
Depth	700 mm
Treadless tyres	yes

ComfortClose	no
Drawer body usable height	400 mm
Usable height	400 mm
with anti-roll lip	yes
Weight	55 kg
maximum load capacity	600 kg
Drawer body height	500 mm
Number of drawers	0
Height	685 mm
Number of doors	0
Number of castors with parking brake	2
Width	750 mm
Electronic locking system can be retrofitted	yes
Number of fixed wheels without parking brake	2
Version	wheeled
Version	for individual configuration
Number of pull-out shelves	0
Casing open at the top	no
Usable height for drawers	400 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Assembly trolley

Accessories

Sheet metal cover top with raised edge on 4 sides
Dimension in G 30X28

951972 30X28