

Garant GRIDLINE

## Roller cabinet for drawers, 20×24G, Height mm / number of drawers: 885/0



### Order data

Order number	931027 885/0
GTIN	4062406352585
Item class	9GK

### Description

#### Version:

To take drawers 20×24G.

Roller cabinet in 24×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

May only be fitted with drawer No. 931046 or No. 931048 (with one-handed individual drawer release system).

### Technical description

Drawer body usable height	600 mm
with anti-roll lip	yes
Number of fixed wheels without parking brake	2

Number of drawers	0
Usable height	600 mm
Depth	700 mm
ComfortClose	no
Drawer body height	700 mm
maximum load capacity	600 kg
Height	885 mm
Number of doors	0
Number of castors with parking brake	2
Treadless tyres	yes
Weight	54 kg
Electronic locking system can be retrofitted	yes
Width	600 mm
Wheel Ø	125 mm
Version	wheeled
Version	for individual configuration
Casing open at the top	no
Number of pull-out shelves	0
Usable height for drawers	600 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x24G
Type of product	Assembly trolley

## Accessories

Lock plate for GridLine Type HU21

914227 HU21

Sheet metal cover top with raised edge on 4 sides  
Dimension in G 24X28

951972 24X28