

Garant GRIDLINE

Roller cabinet for drawers, 26×24G, Height mm / number of drawers: 985/0**Order data**

Order number	931147 985/0
GTIN	4062406352684
Item class	9GK

Description**Version:**

To take drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

May only be fitted with drawer No. 931166 or No. 931168 (with one-handed individual drawer release system).

Technical description

Depth	700 mm
Number of doors	0
ComfortClose	no

Treadless tyres	yes
Width	750 mm
Number of fixed wheels without parking brake	2
Electronic locking system can be retrofitted	yes
Usable height	700 mm
Wheel Ø	125 mm
Weight	65 kg
maximum load capacity	600 kg
with anti-roll lip	yes
Height	985 mm
Number of drawers	0
Drawer body usable height	700 mm
Drawer body height	800 mm
Number of castors with parking brake	2
Version	wheeled
Version	for individual configuration
Number of pull-out shelves	0
Casing open at the top	no
Usable height for drawers	700 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Assembly trolley

Accessories

Sheet metal cover top with raised edge on 4 sides
Dimension in G 30X28

951972 30X28