

Garant GRIDLINE

**Roller cabinet with drawers 75 kg, 36×24G, Height mm / number of drawers:
885/7****Order data**

Order number	931325 885/7
GTIN	4062406272791
Item class	9GK

Description**Version:****Complete with drawers 36×24G.**

Roller cabinet in 40×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

Fitted with:

Drawer front height, mm: 75, 75, 75, 75, 100, 100, 100

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Number of drawers	7
-------------------	---

Individual drawer release system	One-hand
Drawer usable depth	600 mm
Electronic locking system can be retrofitted	yes
Drawer body usable height	600 mm
maximum load capacity	600 kg
Drawer usable depth in G	24
ComfortClose	no
Number of doors	0
Height	885 mm
Drawer/pull-out shelf load capacity	75 kg
Usable height	600 mm
Drawer usable width	900 mm
with anti-roll lip	yes
Drawer usable width in G	36
Drawer runner extension (partial/full extension)	100 %
Number of fixed wheels without parking brake	2
Drawer usable area in G	36×24
Wheel Ø	125 mm
Width	1000 mm
Weight	176 kg
Depth	700 mm
Drawer body height	700 mm
Treadless tyres	yes
Number of castors with parking brake	2
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	600 mm
Casing open at the top	no

Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x24G
Type of product	Assembly trolley

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	931354 75
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	931354 100
Roller cabinet for drawers Height mm / number of drawers 885/0	931327 885/0
Sheet metal cover top with raised edge on 4 sides Dimension in G 40X28	951972 40X28